

Technical data sheet

10 mm² series connectors, polypropylene

Item number: 2056380



Tested to EN 60998.

Steel terminals, steel screws, electrogalvanised, 12-pole, individual terminals detachable from strips using "twist'n'pull".

Captive upwards screw.

Max. approved ambient temperature to EN 60998: -5 to +80 °C.

Nominal cross-section 10 ÷ mm².

Nominal voltage 450 V.

Nominal current 57 A.

Max. attachment each side: 10 mm² single-wire or 6 mm² multi-wire/flexible.




PP Polypropylene

Master data

Item number	2056380
Type	76 CE SW/EKL 2 S
Description 1	Terminal strip
Manufacturer	OBO
Dimension	10,0mm ²
Colour	Black
Material	Polypropylene
Smallest sales unit	10
Unit of quantity	Piece
Weight	4.3 kg
Weight unit	kg/100 pc.

Dimensions



Length	134 mm
Width	23 mm
Height	17 mm

Technical data sheet

10 mm² series connectors, polypropylene

Item number: 2056380



Technical data

Closing plate required	no
Connectable conductor cross-section, single-wire, max.	10 mm ²
Connectable conductor cross-section, single-wire, min.	2.5 mm ²
Connectable conductor cross-section, fine-wire without wire-end ferrule, max.	6 mm ²
Connectable conductor cross-section, fine-wire without wire-end ferrule, min.	2.5 mm ²
Connectable conductor cross-section, multi-wire, max.	6 mm ²
Connectable conductor cross-section, multi-wire, min.	2.5 mm ²
Connection position	Side
No. of terminals	12
Number of screwless terminals per pole	2
Version of electrical connection 1	Screw connection
Version of electrical connection 2	Screw connection
Drill hole spacing, centre	11.5 mm
Explosion-tested version	no
Suitable for flexible conductors	yes
Suitable for solid conductors	yes
Suitable for multi-wire conductors	yes
Mounting type	Direct mounting
Nominal cross-section, min.	10 mm ²
Nominal voltage	450 V
Nominal current	57 A
Pole number	12
Cross-section	Max. attachment each side: 10 mm ² single-wire or 6 mm ² multi-wire/flexible mm ²
Screw tightening torque	0.8 Nm
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-5 °C
Transparent	no
Ambient temperature	80 °C