

Technical data sheet

16 mm² series connectors, polypropylene

Item number: 2056569



Tested to EN 60998.
Steel terminals, steel screws, electrogalvanised, 12-pole, individual terminals detachable from strips using "twist'n'pull".
Captive upwards screw.
Max. approved ambient temperature to EN 60998: -5 to +80 °C.
Nominal cross-section 16 ÷ mm².
Nominal voltage 450 V.
Nominal current 76 A.
Max. attachment each side: 16 mm² single-wire or 10 mm² multi-wire or 6 mm² flexible.



PP

Polypropylene

Master data		
Item number	2056569	
Type	78 CE SW/EKL 3 S	
Description 1	Terminal strip	
Manufacturer	OBO	
Dimension	16,0mm²	
Colour	Black	
Material	Polypropylene	
Smallest sales unit	10	
Unit of quantity	Piece	
Weight	7.5 kg	
Weight unit	kg/100 pc.	


Technical data sheet

16 mm² series connectors, polypropylene

Item number: 2056569



Dimensions



Length	175 mm
Width	25 mm
Height	20.7 mm

Technical data

Closing plate required	no
Connectable conductor cross-section, fine-wire with wire-end ferrule, max.	16 mm ²
Connectable conductor cross-section, fine-wire with wire-end ferrule, min.	4 mm ²
Connectable conductor cross-section, fine-wire without wire-end ferrule, max.	6 mm ²
Connectable conductor cross-section, fine-wire without wire-end ferrule, min.	4 mm ²
Connectable conductor cross-section, multi-wire, max.	10 mm ²
Connectable conductor cross-section, multi-wire, min.	4 mm ²
Connection position	Side
No. of terminals	12
Number of screwless terminals per pole	2
Version of electrical connection 1	Screw connection
Version of electrical connection 2	Screw connection
Drill hole spacing, centre	15 mm
Explosion-tested version	no
Suitable for flexible conductors	yes
Suitable for solid conductors	yes
Suitable for multi-wire conductors	yes
Mounting type	Direct mounting
Nominal cross-section, min.	16 mm ²
Nominal voltage	450 V
Nominal current	76 A

Technical data sheet

16 mm² series connectors, polypropylene

Item number: 2056569



Technical data

Pole number	12
Cross-section	Max. attachment each side: 16 mm ² single-wire or 10 mm ² multi-wire or 6 mm ² flexible mm ²
Screw tightening torque	1.2 kN/m
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-5 °C
Transparent	no
Ambient temperature	80 °C