

Technical data sheet

Plug-in arrester NPE-C50

Item number: 5095609



- Upper part NPE, lightning current combination arrester, type 1+2
- For lightning protection equipotential bonding to VDE 0185-305 (IEC 62305)
 - Lightning current discharge capacity up to 50 kA (10/350) in total
 - Modular, plug-in arrester with dynamic cut-off unit and visual status display
 - Locking mechanism with vibration protection and voltage keying
 - Plastic according to UL 94 V-0



* Complete = Plug-in arrester and base



Master data		
Item number	5095609	
Type	C50-0-255	
Description 1	NPE discharge gap	
Description 2	plug-in arrester	
Manufacturer	OBO	
Dimension	255V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	7.215 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,4832 kg CO2e / 1 Piece	

Technical data sheet

Plug-in arrester NPE-C50

Item number: 5095609



Dimensions



Technical data

	Connection cross-section (min.)	1.5 mm ²
	Response time [N-PE]	100 ns
	Blow-out	no
	Pole version	N/PE
	Structural width in division units (division unit, 17.5 mm)	1
	Operating temperature, max.	80 °C
	Operating temperature, min.	-40 °C
	Lightning surge current (10/350 µs) [N/PE]	50 kA
	Lightning surge current (10/350)	50 kA
	Torque	35 Lbs
	Torque	4 Nm
	Installation location	Interior
	Remote signalling	no
	Follow current quenching capacity (eff) [N-PE]	0.1 kA
	Function/defect display	Visual
	Housing material surge protection components	PA UL 94 V-0
	Maximum continuous voltage AC	255 V
	Integrated back-up fuse	no
	Conductor cross-section, flexible (fine-wire), max.	35 mm ²
	Conductor cross-section, flexible (fine-wire), max.	2 AWG
	Conductor cross-section, flexible (fine-wire), min.	16 AWG
	Conductor cross-section, flexible (fine-wire), min.	1.5 mm ²
	Conductor cross-section, rigid (single-wire/multiwire), max.	2 AWG
	Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
	Conductor cross-section, rigid (single-wire/multiwire), min.	16 AWG
	Conductor cross-section, rigid (single-wire/multiwire), min.	1.5 mm ²
	Humidity, max.	95 %
	Humidity, min.	5 %
	Maximum discharge current (8/20 µs) [N-PE]	80 kA
	Minimum distance	1.5 mm

Technical data sheet

Plug-in arrester NPE-C50

Item number: 5095609



Technical data

Installation type	DIN rail 35 mm
Nominal discharge current (8/20 μ s) [N-PE]	50 kA
Nominal frequency	50 Hz
TN-C-S network form	yes
TN-S network form	yes
TT network form	yes
Pole number	1
Ports	One-Port SPD
Protection rating	IP20
Protective conductor current	< 5 μ A
Protection level [N-PE]	1.5 kV
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-1	Class I+II
SPD to UL 1449	Type 4
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C
TOV voltage [N-PE] – withstand mode – 200 ms	1200 V
Approvals	VDE KEMA UL ÖVE