

Technical data sheet

90° bend for PYROLINE® Con S BSK I90/E30 fire protection duct

Item number: 7215615



90° bend for PYROLINE® Con S BSK I90/E30 fire protection duct, consisting of fibreglass lightweight concrete which is resistant to water and frost for the creation of horizontal changes of direction of the duct. Mounted connectors ensure quick mounting in situ, whilst loosely placed covers ensure quick inspection and reassignment.

Including connection screws and sealing strip.
Including connection screws and sealing strip.



Fibreglass lightweight concrete

Master data

Item number	7215615
Type	BSKH-FB091016
Description 1	90° bend
Description 2	for BSKH I90/E30
Manufacturer	OBO
Dimension	105x160
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Piece
Weight	1010 kg
Weight unit	kg/100 pc.


Technical data sheet

90° bend for PYROLINE® Con S BSK I90/E30 fire protection duct

Item number: 7215615



Dimensions



External dimensions	175 x 260
Internal dimensions	105 x 160
Dimension B	260 mm
Dimension b	160 mm
Dimension h	105 mm
Dimension H	175 mm
Dimension L	380 mm

Technical data

Number of flammable sides	4
Cover fastening	Loose
Fire resistance class E – function maintenance	30
Fire resistance class I – installation duct	90
With perforation	no
Partitions possible	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete
Angle of the bend	90 °