

Technical data sheet

Fire protection duct PYROLINE® Con D BSK I120/E90



Item number: 7215234



Fire protection duct made from water and frost-proof fibreglass light concrete of building material class A1 according to EN 13501-1 for fireproof laying of cables in rescue and emergency routes, and for the maintenance of electrical functionality of safety-relevant systems. Classification I120 as I duct according to DIN 4102 Part 11 and classification E90 as E duct according to DIN 4102 Part 12.

Mounting of the duct directly on walls or under ceilings.

Including countersunk head screws and sealing strips.
Including countersunk head screws and sealing strip.




Fibreglass lightweight concrete

Master data

Item number	7215234
Description 1	Fire protection duct I120/E90
Manufacturer	OBO
Dimension	105x260
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Metre
Weight	3190 kg
Weight unit	kg/100 m

Dimensions



Length	1,000 mm
Dimension B	380 mm
Dimension b	260 mm
Dimension h	105 mm
Dimension H	185 mm

Technical data sheet

Fire protection duct PYROLINE® Con D BSK I120/E90

Item number: 7215234



Technical data

Number of flammable sides	3
Cover fastening	Screw
Fire resistance class E – function maintenance	90
Fire resistance class I – installation duct	120
With perforation	no
Partitions possible	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete