


Technical data sheet

Cavity wall accessory socket, wind-proof

Item number: 2003611



Cavity wall accessory socket, windproof version through soft entry membrane. Dimensions to DIN 49073-1, for plate thickness 7–35 mm. Standard combination spacing 71 mm, option of through-wiring using connection pieces when combining accessory sockets and accessory connection sockets. Accessory sockets can also be used as connection sockets in accordance with VDE 0606-1 with double screw fastening and screw-on cover, protection rating IP40. Twelve connection pieces included. According to IEC 60670-1, IEC 60670-22 and DIN 49073-1.



PP Polypropylene

Master data

Item number	2003611
Type	HG 60 MW
Description 1	Box, empty
Description 2	cavity wall 2K
Manufacturer	OBO
Dimension	Ø68mm, H47mm
Colour	Orange
Material	Polypropylene
Smallest sales unit	25
Unit of quantity	Piece
Weight	2.16 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1905 kg COe / 1 Piece

Technical data sheet


Cavity wall accessory socket, wind-proof

Item number: 2003611



Dimensions

Height	47 mm
--------	-------



Technical data

No. of entries	8
Number of switch boxes	1
Type of entry	soft insertion membrane for NYM cables, data cables and pipes Ø 20 mm
Type of housing penetration	Sealing membrane
Version for	Single
Type	Accessory socket
Device fixing	Screws ,
Equipment	Without
Cover	Without
Cover fastening	Not applicable
Entry from rear	yes
Entries	8
Flame-resistant	Acc. to VDE 0471/DIN 695 Part 2-1, test temperature 850°C
Shape	Round
Milling hole diameter	68 mm
Maintain electrical functions	Without
Floor height, min.	45 mm
for pipe diameter	20 mm
Suitable for plate thickness, max.	35 mm
Suitable for plate thickness, min.	7 mm
Accessory screw clearance	60 mm
Halogen-free	yes
Max. Conductor cross-section	2.5 mm ²
With screening	no
With nail strap	no
With bolts	yes
Mounting type	Cavity wall
Nominal cross-section, max.	2.5 mm ²
Nominal cross-section, min.	1.5 mm ²
Sealable	no

Technical data sheet

Cavity wall accessory socket, wind-proof

Item number: 2003611



Technical data

Impact-resistant	yes
Protection rating	IP40
Support	Without
Airtight	yes
Rated voltage	400 V