


# Technical data sheet

## Cavity wall connection socket with cover

Item number: 2003430



Cavity wall connection box with cover, dimensions to DIN 49073-1, for plate thickness 7–35 mm. 8 break-out openings for NYM cables, data cables and pipes Ø 20 mm, protection rating IP30.  
According to IEC 60670-1, IEC 60670-22 and DIN 49073-1.



**PP** Polypropylene

### Master data

Item number	2003430
Type	HV 70 D
Description 1	Connection plug
Description 2	cavity wall
Manufacturer	OBO
Dimension	Ø74mm, H50mm
Colour	Orange
Material	Polypropylene
Smallest sales unit	10
Unit of quantity	Piece
Weight	3.65 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1215 kg COe / 1 Piece


# Technical data sheet

## Cavity wall connection socket with cover

Item number: 2003430



### Dimensions



Height 50 mm

### Technical data

No. of entries	8
Number of switch boxes	1
Type of entry	break-out openings for NYM cables, data cables and pipes Ø 20 mm
Type of housing penetration	Pre-marking
Version for	Single
Type	Connection socket/box
Equipment	Without
Cover	Not transparent
Cover fastening	Screwed
Cover screw clearance	67 mm
Entry from rear	yes
Entries	8
Flame-resistant	Acc. to VDE 0471/DIN 695 Part 2-1, test temperature 850°C
Shape	Round
Milling hole diameter	74 mm
Maintain electrical functions	Without
Floor height, min.	50 mm
for pipe diameter	20 mm
Suitable for plate thickness, max.	35 mm
Suitable for plate thickness, min.	7 mm
Halogen-free	yes
Max. Conductor cross-section	2.5 mm <sup>2</sup>
With screening	no
With nail strap	no
With bolts	yes
Mounting type	Cavity wall
Nominal cross-section, max.	2.5 mm <sup>2</sup>
Nominal cross-section, min.	1.5 mm <sup>2</sup>
Sealable	no
Impact-resistant	no
Protection rating	IP30
Support	Without
Airtight	no
Rated voltage	400 V