

# Technical data sheet

Device installation trunking Rapid 80, trunking width 130,  
trunking height 70

Item number: 6274502



GK device installation trunking, made of lead-free PVC, suitable for installing directly on the wall or on wall panels. Fastening takes place using the perforation in the trunking. The GK device installation trunking possesses a C profile on the floor to accept a plastic partition. All the switch programmes with a support ring and support clamp design as well as Modul 45 installation devices can be installed in the accessory mounting boxes of series 71GD.... The system opening is 76.5 mm. On each trunking length, a coupling pair is pre-assembled on one side. The cover must be ordered separately.



**PVC** Polyvinylchloride

## Master data

|                                    |                              |
|------------------------------------|------------------------------|
| Item number                        | 6274502                      |
| Type                               | GK-70130LGR                  |
| Description 1                      | Device installation trunking |
| Description 2                      | with base perforation        |
| Manufacturer                       | OBO                          |
| Dimension                          | 70x130x2000                  |
| Colour                             | Light grey; RAL 7035         |
| Material                           | Polyvinylchloride            |
| Smallest sales unit                | 2                            |
| Unit of quantity                   | Metre                        |
| Weight                             | 152 kg                       |
| Weight unit                        | kg/100 m                     |
| CO2 Footprint (GWP) Cradle-to-Gate | 3,0797 kg CO2e / 1 Meter     |


# Technical data sheet

Device installation trunking Rapid 80, trunking width 130,  
trunking height 70

Item number: 6274502



## Dimensions



|        |          |
|--------|----------|
| Length | 2,000 mm |
| Width  | 130 mm   |
| Height | 70 mm    |

## Technical data

|                                   |                       |
|-----------------------------------|-----------------------|
| Number of covers                  | 1                     |
| Number of insertable partitions   | 1                     |
| Rear panel version (inner side)   | Continuous C profile  |
| Rectangular shape                 | yes                   |
| Base perforation                  | With base perforation |
| Halogen-free                      | no                    |
| Cable retaining clip              | no                    |
| Duct connector                    | yes                   |
| Cover mounting type               | Internal              |
| Mounting perforation in base      | yes                   |
| Usable cross-section              | 7600 mm <sup>2</sup>  |
| Cover supplied                    | no                    |
| Cover width                       | 76.5 mm               |
| Protection rating                 | IP30                  |
| Protective film                   | yes                   |
| Protection rating IK code         | IK08                  |
| Symmetrical                       | yes                   |
| Permitted temperature range, max. | 60 °C                 |
| Permitted temperature range, min. | -15 °C                |