

Technical data sheet

IS 8 support

Item number: 6361072



I support with welded head plate. For fastening to horizontal concrete ceilings and steel girders. Single and double-sided brackets of type AS 15, AS 30 and AS 55 can be fastened to the IS 8 K suspended support. The height of the brackets is infinitely adjustable.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6361072
Type	IS 8 K 40 FT
Description 1	Support
Description 2	with welded head plate
Manufacturer	OBO
Dimension	80x42x400
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	321.9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	6,9656 kg CO2e / 1 Piece


Technical data sheet

IS 8 support

Item number: 6361072



Dimensions




Length	400 mm
Width	80 mm
Height	42 mm

Technical data

Version for	I profile
Bracket length 200	9.6 kN
Bracket length 400	7 kN
Bracket length 600	5 kN
Maintain electrical functions	no
Hole width	14 mm
Material thickness	4 mm
Maximum tensile load	50 kN
With tothing	no
Slot width	70 mm

Loads



Load diagram, I support, type IS 8 K

- 1 Bending of the end of the suspended support at permitted bracket load
- 2 Permitted bracket load in kN without man load
- 3 Bracket length in mm
- Load curves with support lengths in mm

Characteristic anchor load values for IS 8 K suspended support

Single-sided load	
	Max. load [kN]
	Bracket width [mm]
Anchor type	<TEXT><P>110</P></TEXT>, <TEXT><P>210</P></TEXT>, <TEXT><P>310</P></TEXT>, <TEXT><P>410</P></TEXT>, <TEXT><P>510</P></TEXT>, <TEXT><P>610</P></TEXT>
BZ3 10x90/0-30	<TEXT><P>4.84</P></TEXT>, <TEXT><P>3.64</P></TEXT>, <TEXT><P>2.92</P></TEXT>, <TEXT><P>2.44</P></TEXT>, <TEXT><P>2.10</P></TEXT>, <TEXT><P>1.83</P></TEXT>
BZ3 12x110/0-35	<TEXT><P>6.60</P></TEXT>, <TEXT><P>5.02</P></TEXT>, <TEXT><P>4.04</P></TEXT>, <TEXT><P>3.37</P></TEXT>, <TEXT><P>2.89</P></TEXT>, <TEXT><P>2.53</P></TEXT>

Max. total load F = cable weight + cable tray + bracket + suspended support. The tabular values for double-sided loads take the available axis spacing $a_i = 10$ cm into account. The stated values are based on uncracked concrete of compressive strength C20/25. Please comply with the installation conditions of ETA(anchors).