

Technical data sheet

Vertical bend, three-compartment, height 28 mm

Item number: 7400644



For vertical direction changes of screed-covered underfloor installation ducts (wall connections, supplies).

An important precondition for correct underfloor installation is the screed structure.

In the case of a screed-covered system, it is important that the screed thickness of the duct is at least 35 mm, to avoid the formation of cracks (DIN 18560).

Screed height: 60 mm only for on-floor connection technology (Telitank), 70 mm or more for underfloor connection technology.



St

Steel

FS

Strip galvanized

Master data

Item number	7400644
Type	KV3 25028
Description 1	Vertical bend
Description 2	3 compartments for EÜK
Manufacturer	OBO
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	213 kg
Weight unit	kg/100 pc.


Technical data sheet

Vertical bend, three-compartment, height 28 mm

Item number: 7400644



Dimensions



Length	200 mm
Width	250 mm
Height	28 mm
Dimension a	90 mm
Dimension b	70 mm
Dimension h	28 mm

Technical data

Number of fixed partitions	2
Number of compartments	3 St.
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Trunking width, min.	250 mm
Duct height, min.	28 mm
Cross-section, draw a	2288 mm ²
Cross-section, draw b	1794 mm ²