

Technical data sheet

Cable tray MKS 35 FT

Item number: 6053106



MKS 35 = Medium duty cable tray system with a side height of 35 mm.
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



St

Steel

FT

Hot-dip galvanised

Master data	
Item number	6053106
Type	MKS 310 FT
Description 1	Cable tray MKS
Description 2	perforated
Manufacturer	OBO
Dimension	35x100x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	153 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	3,6198 kg COe / 1 Meter


Technical data sheet

Cable tray MKS 35 FT

Item number: 6053106



Dimensions



Dimension	35 x 100
Length	3,000 mm
Length	10 ft
Width	100 mm
Width	4 in
Height	35 mm
Plate thickness	0.04 in
Plate thickness	1 mm
Dimension B	100 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	33 cm ²
Usable cross-section	3300 mm ²
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Technical data sheet


Cable tray MKS 35 FT

Item number: 6053106



Loads

Insertable support spacings, min.	1 m
Insertable support spacings, max.	3 m
Support spacing 1.0 m	1.2 kN/m
Support spacing 1.5 m	0.75 kN/m
Support spacing 2.0 m	0.55 kN/m
Support spacing 2.5 m	0.3 kN/m
Support spacing 3.0 m	0.2 kN/m



Load diagram, cable tray, type MKS 35

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width