

Technical data sheet

Lightning current arrester, 1-pole with function display

Item number: 5096851



Lightning arrester with visual function display, type 1, in accordance with DIN EN 61643-11 for interface 0 to 1 (LPZ) in accordance with lightning protection concept to IEC 61312-1 and VDE 0185-305 (IEC 62305)

- Upper part and base, plug-in upper part
- Arresting capacity 50 kA (10/350 μ s) per pole
- Voltage protection level < 2.0 kV
- Power consumption < 26 mW/pole
- Line following current quenching 25 kA Ipeak
- Incl. plug caps for labelling the connections
- Encapsulated, non-extinguishing spark gap: can be used in standard distributor housings

Application example: Industrial systems.


Note: Requires as a decoupling length for surge protection 5 m of cable.



Master data

Item number	5096851
Type	MC 50-B-OS
Description 1	LightningController
Description 2	with function display
Manufacturer	OBO
Dimension	255V
Smallest sales unit	1
Unit of quantity	Piece
Weight	34.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	2,0707 kg CO2e / 1 Piece

Dimensions



Length	100 mm
Width	35 mm
Height	69 mm

Technical data sheet

Lightning current arrester, 1-pole with function display

Item number: 5096851



Technical data

Arrester surge current (8/20 µs) [total]	50 kA
Response time	<100 ns
Blow-out	no
Pole version	1
Structural width in division units (division unit, 17.5 mm)	2
Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	50 kA
Lightning surge current (10/350)	50 kA
Explosion-tested version	no
Remote signalling	no
Maximum continuous voltage AC	255 V
Conductor cross-section, rigid (single-wire/multiwire), max.	50 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	10 mm ²
Lightning protection zone LPZ	0→1
Max. mains-side overcurrent protection	500
Maximum back-up fuse	500 A
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	50 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	Other
Test class, type 1	yes
Protection rating	IP20
Protection level	≤2,0 kV
Signalling on device	Visual
SPD to EN 61643-11	Type 1
SPD to IEC 61643-1	Class I
Permitted temperature range, max.	85 °C
Permitted temperature range, min.	-40 °C