


# Technical data sheet

## Cable tray SKS 60 A4

Item number: 6056759



SKS 60 = Heavy-duty cable tray system with 60 mm side height.  
The cable tray, type SKS, should also be used for maintenance of electrical function. For additional data, please refer to BSS fire protection systems. The cable tray is fastened to the bracket with bolts, type FRS M6 x 12.  
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



A4	Stainless steel
2B	Bright, treated

### Master data

Item number	6056759
Type	SKS 640 A4
Description 1	Cable tray SKS
Description 2	perforated
Manufacturer	OBO
Dimension	60x400x3000
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	3
Unit of quantity	Metre
Weight	553.667 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	30,7161 kg CO2e / 1 Meter


# Technical data sheet

## Cable tray SKS 60 A4

Item number: 6056759



### Dimensions



Length	3,000 mm
Length	10 ft
Width	400 mm
Width	16 in
Height	60 mm
Height	2 in
Plate thickness	0.06 in
Plate thickness	1.5 mm
Dimension B	400 mm
Maß W	400 mm

### Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Maintain electrical functions	yes
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	238 cm <sup>2</sup>
Usable cross-section	23800 mm <sup>2</sup>
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

# Technical data sheet

## Cable tray SKS 60 A4

Item number: 6056759



### Loads

Insertable support spacings, min.	1.5 m
Insertable support spacings, max.	3 m
Support spacing 1.5 m	2.65 kN/m
Support spacing 2.0 m	1.8 kN/m
Support spacing 2.5 m	1.15 kN/m
Support spacing 3.0 m	0.5 kN/m

