Technical data sheet

Junction box T 350, plug-in seal

Item number: 2007125





Junction box for the connection of cables and lines indoors and in protected outdoor areas. Rectangular design with plug-in seals to the sides and knock-out entries in the bottom. Suitable for wall and ceiling mounting and on mounting panels. With the option to fasten inside and to mount via the corner domes. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK05 according to DIN EN 50102.









Polypropylene, fibreglass reinforced















2007125
T 350
Junction box
with entries
OBO
285x201x120
Light grey; RAL 7035
Polypropylene, fibreglass reinforced
1
Piece
63 kg
kg/100 pc.
2,7525 kg COe / 1 Piece

Technical data sheet

Junction box T 350, plug-in seal





Length	285 mm
Width	201 mm
Height	120 mm

Technical data

Expandable	ves
No. of entries	24
Type of insertion	Plug-in seal
Type of entry	Cable
Type of housing penetration	Cuttable stepped membrane
Measured insulation voltage Vi	500 V
Equipment	Without
Cover	Not transparent
Cover fastening	Screwed
Entry from rear	ves
Entries	16 x M32
Littles	8 x M40
Explosion-tested version	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
Shape	Rectangular
Maintain electrical functions	Without
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
Fibre-glass reinforced	yes
Halogen-free	yes
Clear internal dimensions	267x182x110 mm
With screening	no
with lid	yes
Mounting type	Wall/ceiling mounting
Nominal cross-section, min.	35 mm ²
Nominal voltage	500 V
Sealable	yes
Protection rating	IP66
Protection rating IK code	IK05.
Permitted temperature range,	60 °C
max.	 -5 °C
Permitted temperature range, min.	-5 C
Transparent lid	no
Weatherproof	no