

# Technical data sheet

## US 7 support A2

Item number: 6338658



Suspended support (U profile) with welded head plate.  
For fastening to horizontal concrete ceilings and steel girders. For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 61.



**A2** Stainless steel

**2B** Bright, treated

### Master data

Item number	6338658
Type	US 7 K 60 A2
Description 1	Support
Description 2	with welded head plate
Manufacturer	OBO
Dimension	70x50x600
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	337 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	19,3642 kg CO2e / 1 Piece


# Technical data sheet

## US 7 support A2

Item number: 6338658



### Dimensions



Length	600 mm
Width	70 mm
Height	50 mm

### Technical data

Type of perforation	3 sides perforated
Version for	U profile
Bracket length 200	8.3 kN
Bracket length 400	5 kN
Bracket length 600	3.5 kN
Maintain electrical functions	no
Material thickness	4 mm
Maximum tensile load	11 kN

### Loads



#### Load diagram, U support, type US 7 K VA

- 1** Bending of the end of the suspended support at permitted bracket load
- 2** Permitted bracket load in kN without man load
- 3** Bracket length in mm
- Load curves with support lengths in mm

### Characteristic anchor load values for U support, type US 7 K

Single-sided load	
	Max. load [kN]
Anchor type	Bracket width [mm]
	<P>110%</P>, <P>210</P>, <P>310</P>, <P>410</P>, <P>510</P>, <P>610</P>
BZ3 10x90/0-30	<P>3.97</P>, <P>3.03</P>, <P>2.44</P>, <P>2.04</P>, <P>1.76</P>, <P>1.54</P>
BZ3 12x110/0-35	<P>5.16</P>, <P>3.90</P>, <P>3.15</P>, <P>2.64</P>, <P>2.27</P>, <P>1.99</P>

Max. total load  $F = \text{cable weight} + \text{cable tray} + \text{bracket} + \text{suspended support}$ . The tabular values for double-sided loads take the available axis spacing  $a_i = 10 \text{ cm}$  into account. The stated values are based on uncracked concrete of compressive strength C20/25. Please comply with the installation conditions of ETA(anchors).