

Technical data sheet

Base V20 and V25 3pole +NPE with remote signaling

Item number: 5095859



Base


- Suitable for V 25-B+C or V 20-C and C 25-B+C
- With remote signalling and potential-free changeover contact for function monitoring
- Pre-mounted and ready for connection
- With protection against incorrect insertion
- For TN-S and TT network systems
- Labelled connections



Master data

Item number	5095859
Type	V20-C U-3+NPE-FS
Description 1	Bottom part V20 and V25
Description 2	with remote signalling + NPE
Manufacturer	OBO
Dimension	3+NPE+FS
Smallest sales unit	1
Unit of quantity	Piece
Weight	34 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,16 kg CO2e / 1 Piece

Dimensions



Technical data sheet

Base V20 and V25 3pole +NPE with remote signaling

Item number: 5095859



Technical data

Version for	3-pole with NPE; with RS; base
Pole version	3+N/PE
Structural width in division units (division unit, 17.5 mm)	5
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Protection rating	IP20
Signalling on device	None
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C