

Technical data sheet

Combination arrester V25, 3-pole 280 V

Item number: 5094423



Combination arrester, lightning and surge arrester type 1+2

- Complete unit consisting of upper part and base, pre-mounted and ready for connection
- For TN systems
- Plug-in arrester with dynamic cut-off unit
- With visual function display
- Protection level decoded:705:Value:RAM1; kV
- Encapsulated, non-extinguishing zinc oxide varistor arrester for use in standard distributor housings
- Labelled connections

Application example: Buildings with open-wire power supply or for setting up lightning protection equipotential bonding in residential buildings.


* Complete = Plug-in arrester and base



Master data

Item number	5094423
Type	V25-B+C 3-280
Description 1	CombiController V25
Description 2	3-pole version
Manufacturer	OBO
Dimension	280V
Smallest sales unit	1
Unit of quantity	Piece
Weight	42.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,2614 kg CO2e / 1 Piece

Dimensions



Technical data sheet

Combination arrester V25, 3-pole 280 V

Item number: 5094423



Technical data

	Arrester surge current (8/20 µs) [total]	90 kA
	Response time	<25 ns
	Blow-out	no
	Version for	3-pole
	Pole version	3
	Structural width in division units (division unit, 17.5 mm)	3
	Operating temperature, max.	80 °C
	Operating temperature, min.	-40 °C
	Lightning surge current (10/350 µs)	7 kA
	Lightning surge current (10/350 µs) [N/PE]	25 kA
	Lightning surge current (10/350 µs) [L-N]	21 kA
	Remote signalling	no
	Follow current quenching capacity leff	25 kA
	Maximum continuous voltage AC	280 V
	Maximum continuous voltage DC	200 V
	Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
	Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
	Lightning protection zone LPZ	0→2
	Max. mains-side overcurrent protection	160
	Maximum back-up fuse	160 A
	Maximum discharge current (8/20 µs)	50 kA
	Nominal discharge current (8/20 µs)	30 kA
	Nominal discharge current (8/20 µs) [L-N]	30 kA
	Nominal discharge current (8/20 µs) [N-PE]	30 kA
	Nominal voltage AC (50/60 Hz)	230 V
	Network form	Other
	TN network form	yes
	TN-C network form	yes
	Pole number	3
	Test class, type 2	yes
Protection rating	IP20	
Protection level	≤0,9 kV	
Signalling on device	Visual	
SPD to EN 61643-11	Type 1+2	
SPD to IEC 61643-1	Class I+II	
Permitted temperature range, max.	80 °C	
Permitted temperature range, min.	-40 °C	