

Technical data sheet

MCR protection for 2-pole for power supply with leak current-free remote signalling, 230 V AC/DC
Item number: 5097939



Type 3 surge protection/fine network protection to EN 61643-11 with leak current-free remote signalling

- With remote signalling: potential-free NC contact for function monitoring
- With installation-friendly, screwless connection terminals
- In space-saving 17.5 mm grid
- Y circuit

Application: Universal use on 35 mm DIN profile rails in any standard distributor housing.



Master data		
Item number	5097939	
Description 1	Lightning barrier	
Description 2	with remote signalling	
Manufacturer	OBO	
Dimension	230V AC	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	6 kg	
Weight unit	kg/100 pc.	


Technical data sheet

MCR protection for 2-pole for power supply with leak current-free remote signalling, 230 V AC/DC

Item number: 5097939



Dimensions



Technical data



Response time	<25 ns
Blow-out	no
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
FM contacts	NC contact
Maximum continuous voltage AC	255 V
Maximum continuous voltage DC	350 V
Conductor cross-section, rigid (single-wire/multiwire), max.	2.5 mm²
Conductor cross-section, rigid (single-wire/multiwire), min.	0.14 mm²
Lightning protection zone LPZ	2→3
Maximum discharge current (8/20 µs)	7 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	2.5 kA
Network form	Other
OBO_Nominal load current (input/ output terminal)	20 A
Pole number	3
Test class, type 3	yes
Protection rating	IP20
Protection level [L-N]	≤1000
Protection level wire-wire	< 1000 V
Protection level wire-earth	< 1400 V
Signalling on device	None
SPD to EN 61643-11	Type 3
SPD to IEC 61643-1	Class III
Cable type for surge protection devices	Power cable AV