

# Technical data sheet

## Wide span cable ladder WKLG 110 A2

Item number: 6311214



Wide span cable ladder with perforated side rails of side height of 110 mm. Fastening of cables with clamp clip, type 2056.



Straight connectors of type WRVL 110 should be ordered separately and in the appropriate quantity.  
Magnetic shield insulation without cover 10 dB, with cover 15 dB.



**A2** Stainless steel

**2B** Bright, treated

### Master data

Item number	6311214
Type	WKLG 1150 A2
Description 1	Wide span cable ladder
Description 2	perforated side rail
Manufacturer	OBO
Dimension	110x500x6000
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	6
Unit of quantity	Metre
Weight	628.866 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	31,9939 kg CO2e / 1 Meter


# Technical data sheet

## Wide span cable ladder WKLG 110 A2

Item number: 6311214



### Dimensions



Dimension	110x500
Length	6,000 mm
Width	500 mm
Height	110 mm
Dimension B	500 mm
Dimension L	6,000 mm
Rung slot dimension	17.00

### Technical data

Version of the rungs	Profile perforated
Side rail version	Profile (open)
Fastening of rung	Fully riveted
Mounting system fastening type	Floor Ceiling Wall
Maintain electrical functions	no
Usable cross-section	471 cm <sup>2</sup>
Usable cross-section	47100 mm <sup>2</sup>
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	yes
Rail thickness	2 mm

# Technical data sheet


## Wide span cable ladder WKLG 110 A2

Item number: 6311214



### Loads

Insertable support spacings, min.	3 m
Insertable support spacings, max.	7 m
Support spacing 3.0 m	2.3 kN/m
Support spacing 3.5 m	2.25 kN/m
Support spacing 4.0 m	2.1 kN/m
Support spacing 4.5 m	1.83 kN/m
Support spacing 5.0 m	1.5 kN/m
Support spacing 6.0 m	1 kN/m
Support spacing 7.0 m	0.7 kN/m



Load diagram, wide span cable ladder, type WKLG 110

- 1** Permitted cable tray/ladder load in kN/m without man load
- 2** Support width in m
- 3** Rail bend in mm at permitted kN/m
- 4** Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width